

# Airnet® II

2 Channel Particle Sensor

AVAILABLE WITH  
**ISO 17025**  
CALIBRATION  
for select parameters



The Airnet® II particle sensor makes it easy and cost-effective to monitor your cleanroom. This particle sensor offers a small footprint, unparalleled performance, and data transmission capabilities while meeting the specification of ISO 21501-4 and ISO 14644-1:2015.

Simple installation with versatile power options, the unit can be configured to accept distributed power from an in-house system, local power plug-in, or Power over Ethernet (PoE). Communication capabilities include Ethernet to interface with Pharmaceutical Net, Facility Net, or FacilityPro® software, Modbus communications, or optional 4-20 mA output.

Data integrity is maintained through the use of a data queue feature that continues to gather data even if network communication is lost.

To ensure proper flow conditions and vacuum system operation, these units incorporate a Dynamic Flow Sensing system that will alarm with a 15% change in flow conditions.

For applications where decontamination using Vaporized Hydrogen Peroxide (VHP) is required, an optional VHP-compatible unit is available for a simple installation without complex valving (Airnet 510XR).

## BENEFITS

- Proven technology provides reliable and accurate data
- Allows for immediate reaction to particle contamination events
- A low-cost solution for multipoint monitoring
- Interfaces with Facility Net, Pharmaceutical Net and FacilityPro Software for comprehensive management of cleanroom conditions
- A small footprint and flexible mounting options make it easy to install in cleanrooms and mini-environments
- A laser diode (LD) drastically reduces the need for maintenance and extends product lifecycle
- Automatic laser shutdown reduces laser failures
- Data queue maintains data integrity when communication is lost
- Optional 4-20 mA output for integration with existing systems to help you understand your environment and communicate with other systems
- Optional XR coating protects sensors against corrosive or oxidizing vapors in VHP sterilization processes

## FEATURES

- 2 channels
- 0.5 and 5.0  $\mu\text{m}$  size range, suitable for Pharmaceutical application
- 1.0 CFM flow rate
- Interfaces with Modbus communications and optional 4-20 mA output
- Chemical-resistant polycarbonate (PC) enclosure
- Low sample point cost
- Small enough for use in remote locations
- ISO14644-1:2015 Compliant

## APPLICATIONS

- Cleanroom monitoring
- Dedicated monitoring of critical locations
- Trend analysis
- Statistical process control
- Multi-location monitoring
- Isolator monitoring



**PARTICLE  
MEASURING  
SYSTEMS®**  
a spectris company

*Without measurement there is no control*

# Airnet® II

## 2 Channel Particle Sensor

### Specifications

	301	501/501A	510	510XR
<b>Size Range</b>	0.3, 0.5 µm	0.5, 5.0 µm <sup>1</sup>	0.5, 5.0 µm	0.5, 5.0 µm
<b>Flow Rate</b>	0.1 CFM (2.8 LPM)	0.1 CFM (2.8 LPM)	1.0 CFM (28.3 LPM)	1.0 CFM (28.3 LPM)
<b>Counting Efficiency</b>	50% ± 20% for most-sensitive channel. Meets ISO 21501-4 100% ± 10% at 1.5 to 2.0 times channel one size. Meets ISO 21501-4			
<b>Zero Count</b>	≤ 70.7 counts/m <sup>3</sup>	≤ 70.7 counts/m <sup>3</sup>	≤ 7.07 counts/m <sup>3</sup>	≤ 7.07 counts/m <sup>3</sup>
<b>Maximum Concentration<sup>2</sup></b>	5,695,168/ft <sup>3</sup>	9,578,238/ft <sup>3</sup>	957,824/ft <sup>3</sup>	957,824/ft <sup>3</sup>
<b>Laser Source</b>	Diode			
<b>Laser Classification</b>	Class 1 per EN60825 (Internally, a Class IIIB laser is used, per EN60825)			
<b>Exterior Surface</b>	Polycarbonate			
<b>Dimensions (H x W x L)</b>	5.3 x 3.6 x 3.8 in (13.5 x 8.9 x 9.6 cm)	5.3 x 3.6 x 3.8 in (13.5 x 8.9 x 9.6 cm)	5.3 x 3.6 x 3.8 in (13.5 x 8.9 x 9.6 cm)	5.3 x 3.6 x 3.8 in (13.5 x 8.9 x 9.6 cm)
<b>Weight</b>	1.6 lb (0.73 kg)	1.6 lb (0.73 kg)	1.6 lb (0.73 kg)	1.6 lb (0.73 kg)
<b>Sample Probe or Tubing</b>	1/4" ID	1/4" ID	1/4" ID	1/4" ID
<b>Flow System</b>	External vacuum 1/4" connection; automatic laser shutoff and alarm on 15% flow variation			
<b>Vacuum Source</b>	> 11 in Hg (> 375 mBar) below atm pressure	> 11 in Hg (> 375 mBar) below atm pressure	> 15 in Hg (> 410 mBar) below atm pressure	> 15 in Hg (> 410 mBar) below atm pressure
<b>Power</b>	24 VDC (0.5 A) 100 – 240 VAC ± 10%, 50 – 60 Hz, Power Supply (optional), or use of Power over Ethernet 48 VDC via a PoE router			
<b>Communication Connectors</b>	Ethernet (Particle Measuring Systems proprietary protocol, Modbus TCP) RS-232 (configuration and diagnostic tool only, no data) 4-20 mA (optional) (3 output channels: 2 particle data, 1 instrument status)			
<b>Status Indicators</b>	Programmable status (two-color LED), Activity (one-color LED)			
<b>Calibration</b>	Calibration materials used are traceable to the National Institute of Standards and Technology (NIST) and meet ISO 21501-4 requirements			
<b>Environment</b>	Temperature: 4 – 35 °C, 5 – 95%; non-condensing relative humidity			
<b>Complies with</b>	EU RoHS, ISO 21501-4, ISO 14644-1:2015			

<sup>1</sup> Airnet II 501A has 0.5 and 1.0 µm channels.

<sup>2</sup> 10% coincidence loss at maximum concentration.

Airnet®, FacilityPro® and IsoAir® are registered trademarks of Particle Measuring Systems, Inc. All other trademarks are the property of their respective owners. Particle Measuring Systems, Inc. reserves the right to change specifications without notice. © 2018 Particle Measuring Systems, Inc. All rights reserved.



**PARTICLE MEASURING SYSTEMS®**  
a spectris company

### HEADQUARTERS

5475 Airport Blvd  
Boulder, Colorado 80301 USA  
T: +1 303 443 7100, +1 800 238 1801

**Instrument Service & Support**  
T: +1 800 557 6363

**Customer Response Center**  
T: +1 877 475 3317  
E: info@pmeasuring.com

### GLOBAL OFFICES

**AUSTRIA**  
T: +43 1 71 728 285  
E: pmsaustria@pmeasuring.com

**BENELUX**  
T: +32 10 23 71 56  
E: pmsbelgium@pmeasuring.com

**BRAZIL**  
T: +55 11 5188 8227  
E: pmsbrazil@pmeasuring.com

**CHINA**  
T: +86 21 6113 3600  
E: pmschina@pmeasuring.com

**FRANCE**  
T: +33 (0)1 60 10 32 96  
E: pmsfrance@pmeasuring.com

**GERMANY**  
T: +49 6151 6671 632  
E: pmsgermany@pmeasuring.com

**ITALY**  
T: +39 06 9053 0130  
E: pmsrli@pmeasuring.com

**JAPAN**  
T: +81 3 5298 8175  
E: pmsjapan@pmeasuring.com

**KOREA**  
T: +82 31 286 5790  
E: pmskorea@pmeasuring.com

**MEXICO**  
T: +52 55 2271 5106  
E: pmsmexico@pmeasuring.com

**NORDIC**  
T: +45 707 028 55  
E: pmsnordic@pmeasuring.com

**PUERTO RICO**  
T: +1 787 718 9096  
E: pmspuertorico@pmeasuring.com

**SINGAPORE**  
T: +65 6496 0330  
E: pmsingapore@pmeasuring.com

**SWITZERLAND**  
T: +41 71 987 01 01  
E: pmsswitzerland@pmeasuring.com

**TAIWAN**  
T: 886-3-5525300 Ext: 301  
E: pmstaiwan@pmeasuring.com

**UNITED KINGDOM**  
T: +44 1684 581 000  
E: pmsemea@pmeasuring.com